TSA PRM470

Screen people, vehicles or areas with a small, lightweight hand-held personal radiation monitor.

Versatile On Demand Screening

Easy-to-Operate

Day or Night Operation

Cost Effective Primary or Secondary Screening



The TSA PRM470 personal hand-held radiation monitor is ideal for searching at plant exits and material access areas, as well as contamination and background monitoring. The small size, light weight, and long battery life make it ideal for searching vehicles that require extended search times. The PRM470 hand-held is a popular choice for locating radioactive sources and measuring intensity in the field.

Advanced Design Features

The TSA PRM470 uses low power electronics to provide up to 17 hours of continuous operation from the rechargeable batteries. The PRM470 also features a self-test during power up, automatic background count and user determined alarm settings. Detection information and parameters are easy to read on the backlit display that can be used in dark or light conditions.

Programmable Detection Parameters

Settings may be configured from the front panel, or from a personal computer.

Easy-to-Operate

The TSA PRM470 is typically ready to use within 20 seconds of start-up. The PRM470 features an audio and visual search/find mode to assist in pinpointing radioactive sources. The PRM470 uses a motion switch to automatically switch from background to search mode when the instrument is moved. After the instrument has been at rest for a preset duration, it will revert to background update. The unit may be programmed by the user to scale the display to CPS, $\mu Sv/hr$ or mR/hr. This conversion is not energy compensated. Therefore, the value displayed is only an approximation of actual dose rate.

As detected counts increase, so does the frequency of the audio signal helping to pinpoint the location of the radioactive source. LED indicators respond in similar fashion, flashing faster as counts increase. On gamma and neutron instruments, the LED indicators also assist to identify the type of radiation being detected (a red LED for gamma, and blue LED for neutron radiation).

A serial port is available for managing detection parameters and controlling security levels for the individual unit from a computer.

Flexible Detection Options

The TSA PRM470 is available in three configurations; Gamma, Neutron or a combination of Gamma and Neutron detection. Gamma provides detection of ionizing radiation and Neutron provides detection of Special Nuclear Materials (SNM) while the combined Gamma and Neutron provides the most powerful detection capabilities for radioactive isotopes even in shielded materials.

Standard Features

Programmable Detection Parameters
Programmable Security Levels
Audio and Visual Indicators
Universal Power Supply
Serial Port Connectivity
NmHi Battery Pack

Markets

Aviation

Critical Infrastructure

Customs and Border Control

Defense

Law Enforcement

First Responders

Event Security

Ports



TSA PRM470

Specifications

Sensitivity Will detect 10g HEU or 1g ²³⁹Pu when tested in accordace with

ASTM Standard C 1237

Detectors **Gamma**: One, 3.5 h x 2.88 w x 1.24 d in. (8.8 x 7.2 x 3.1 cm)

organic plastic scintillator detector; provides approximately 12.6

in³ (206cc) of detector volume.

Neutron: Two, He³ tube, 4 in. (10.2 cm) active, 4 ATM. Gamma and Neutron: One, 3.5 h x 2.88 w x 1.24 d in. (8.8 x 7.2 x 3.1 cm) organic plastic scintillator detector; provides approximately 12.6 in³ (206 cc) of detector volume and one, He³

tube, 4 in. (10.2cm) active, 4 ATM.

Alarm Level User configurable from 0.1 to 9.9 sigma

Audible tone and LED Alarm Indication

Count Time Gamma search mode: 0.05 sec. count with 0.4 sec. moving

average. Neutron: 1 sec. count time. Background time: Operator

configurable

Display Alphanumeric LCD, 4 lines x 16 characters, with back-light

Power Requirements Internal rechargeable battery pack

Dimensions Box = $7.75 \text{ h} \times 4.75 \text{ w} \times 3.5 \text{ d}$ in. (19.7 x 12.06 x 8.9 cm)

Handle = 4.75 h x 2.75 w x .75 d in. (12.06 cm x 7.00 cm x 1.90

Weight 2.4 lb (1.1 kg) with batteries Environmental 32° to 100°F (0° to 38°C)

*ASTM Standard C 1237 is available from your Rapiscan Systems sales representative or The American Society for Testing and Materials, 100 Barr Harbor Drive, West Conshohocken, PA 19428 (610) 832-9585

Definitions

Gamma Detection - For the detection of ionizing radiation.

Neutron Detection - Typically used to detect Special Nuclear Materials (SNM).

Gamma and Neutron Detection - For full spectrum detection capabilities.

Options

Replaceable Alkaline Battery

Serial Port

With continual development of our products Rapiscan Systems reserves the right to amend specifications without notice. Product pictures are for general reference. Please note that due to US laws and regulations, not all Rapiscan products are available for sale in all countries without restriction. Please contact your Rapiscan Systems sales representative for more information.

Rapiscan systems

An OSI Systems Company

www.rapiscansystems.com

240 Macpherson Road

Singapore 348574 SINGAPORE Tel:

sales@rapiscansystems.com

+65-6846-3511 +65-6743-9915

RAPISCAN RADIATION DETECTION PRODUCT LINE HEADQUARTERS

14000 Mead Street Longmont, Colorado 80504 UNITED STATES of AMERICA Tel: +1 970-535-9949 Fax: +1 970-535-3285 AMERICAS, CARIBBEAN 2805 Columbia Street Torrance, California 90503 UNITED STATES of AMERICA

+1 310-978-1457

EUROPE, MIDDLE EAST, AFRICA

+44 (0) 870-7774301

+44 (0) 870-7774302

#07-01 Pines Industrial Building

Fax: +1 310-349-2491

X-Ray House

Bonehurst Road Salfords

Surrey RH1 5GG UNITED KINGDOM

WFB

Fax:

Fax:

www.rapiscansystems.com